

General Industrial Products



Scotch® Premium Vinyl Electrical Tape Super 88



Features:

- Polyvinyl chloride backing
- Pressure-sensitive rubber adhesive
- Compatible with solid dielectric cable insulations, rubber and synthetic compounds and epoxy and polyurethane resins
- Inhibits corrosion of electrical conductors
- Excellent resistance to abrasion, moisture, alkalis, acids, corrosion and varying weather conditions
- Made in the USA
- Designed to perform continuously in ambient temperatures up to 105 °C (220 °F)
- Primary electrical insulation for all wires and cable splices rated up to 600 V and 105 °C (220 °F)
- Primary electrical insulation for 600 V bus applications and protective jacketing for low and high voltage bus and repairs
- Harnessing of wires and cables
- UL® listed
- CSA certified

Item No.	Mfr. No.	Width (in)	Length (ft)	Pkg. Qty.
102172089	00-054007-06143-4	3/4	66	10

3M™ Temflex™ General Use Vinyl Electrical Tape 1700



Features:

- Good quality, economical, general-purpose vinyl insulating tape
- Excellent resistance to abrasion, moisture, alkalis, acids, corrosion and varying weather conditions
- Flame-retardant and conformable
- Excellent mechanical protection with minimal bulk
- Primary electrical insulation for all wire and cable splices rated up to 600 V
- Protective jacketing for high voltage cable splices and repairs
- Harnessing of wires and cables
- For indoor or outdoor applications
- For above or below grade applications
- UL® listed
- CSA certified

Item No.	Mfr. No.	Width (in)	Length (ft)	Color
102171819	00-054007-69764-0	3/4	60	Black

3M™ General Use Masking Tape 201+



Features:

- General use tape for light and medium duty applications
- Rubber-based adhesive sticks to a variety of surfaces
- Smooth and conformable crepe paper backing is easy to handle, apply and remove in one piece
- Easily hand tearable, yet resists slivering
- Temperature resistant up to 200 °F (66 °C) for 30 minutes
- Offered in bulk and individually wrapped rolls
- Use for holding, bundling, sealing, non-critical masking applications and a vast number of other jobs where a pressure sensitive tape is needed

Item No.	Mfr. No.	Width (mm)	Length (m)	Thickness (mil)
106269920	00-051115-64746-8	24	55	4.4
106277292	00-051115-64747-5	36	55	4.4
106287642	00-051115-64748-2	48	55	4.4



Scotch® Super 33+™ Vinyl Electrical Tape



Features:

- Polyvinyl chloride backing
- Pressure-sensitive rubber adhesive
- Compatible with solid dielectric cable insulations, rubber and synthetic compounds and epoxy and polyurethane resins
- Inhibits corrosion of electrical conductors
- Conformable for cold weather applications down to -18 °C (0 °F)
- Excellent resistance to abrasion, moisture, alkalis, acids, corrosion and varying weather conditions
- Provides moisture-tight electrical and mechanical protection with minimum bulk

- Made in the USA
- Designed to perform continuously in ambient temperatures up to 105 °C (220 °F)
- For indoor or outdoor applications
- Primary electrical insulation for all wires and cable splices rated up to 600 V and 105 °C (220 °F)
- Primary electrical insulation for 600 V bus applications
- Protective jacketing for high voltage cable splices and repairs
- Harnessing of wires and cables
- UL® listed
- CSA certified

Item No.	Mfr. No.	Width (in)	Length (ft)	Pkg. Qty.
102172087	00-054007-06133-5	3/4	52	10
102171280	00-054007-06132-8	3/4	66	10



Scotch® Filament Tape 897



Features:

- Polypropylene film
- Abrasion- and moisture-resistant
- High tensile strength (170 lb/in width)
- Allows printing and illustrations to be seen through tape
- Good shear and initial adhesion
- Good aging
- Protective of filaments and adhesive to provide longer package life
- Maximizes package performance when exposed to outdoor and humid environments
- Good holding under wide range of application conditions with minimum amount of tape
- Holds with minimum riddown
- Boxes remain closed for longer periods of time
- Light-duty strapping, building and reinforcing

Adhesion Strength: 60 oz/in
Thickness: 6 mil

Item No.	Mfr. No.	Width (mm)	Length (m)	Color
101383669	00-021200-86524-4	18	55	Clear
101400742	00-021200-86525-1	24	55	Clear



Don't Forget...

Visit us online at Applied.com!

