

**CRESCENT 2 Piece Tongue & Groove Pliers Set**



**Features:**

- Unique tooth design for better grip – increases torque with less effort
- “V” jaws allow for firmer grip on various shapes
- Alloy steel construction with induction hardened teeth maximizes durability
- Integrated non-marring pipe grip area in handle made of high impact rubber
- Exposed steel handle tips designed to prevent handle pull-off and allow for reaming and tightening tub drains
- Corrosion-resistant black oxide finish

Item No.	Mfr. No.	Length (in)
113454389	RT400SGSET2	10 & 12



**Straight Jaw Tongue & Groove Pliers**



**Features:**

- CHANNELLOCK BLUE® grips for comfort
- Undercut tongue and groove design won't slip
- Right angle, laser heat-treated teeth grip better and last longer
- Patented reinforcing edge minimizes stress breakage
- CHANNELLOCK® uses high carbon C1080 steel for superior performance on the job and specially coated for ultimate rust prevention
- PermaLock® fastener eliminates nut and bolt failure
- Made in the USA

Item No.	Mfr. No.	Capacity (in)	Jaw Length (in)	Overall Length (in)
111193072	424	0.50	0.33	4 1/2
111193076	426	0.87	0.81	6 1/2
110375569	420	1.50	1.12	9 1/2
111193080	430	2.00	1.38	10
101868542	440	2.25	1.50	12
110553578	460	4.25	2.56	16 1/2
111192917	480	5.50	3.00	20 1/2



**V-Jaw Tongue & Groove Pliers**



**Features:**

- CHANNELLOCK BLUE® grips for comfort
- Undercut tongue and groove design won't slip
- Right angle, laser heat-treated teeth grip better and last longer
- Patented reinforcing edge minimizes stress breakage
- Uses high carbon C1080 steel for superior performance on the job and specially coated for ultimate rust prevention
- V-jaws give you more points of contact on round stock and tubing
- PermaLock® fastener eliminates nut and bolt failure
- Made in the USA

Item No.	Mfr. No.	Capacity (in)	Jaw Length (in)	Overall Length (in)
111193057	422	1 1/2	1.12	9 1/2
111193091	442	2 1/4	1.50	12



**Tongue & Groove Plier Set**



**Features:**

- CHANNELLOCK BLUE® grips for comfort
- Undercut tongue and groove design won't slip
- Right angle, laser heat-treated teeth grip better and last longer
- PermaLock® fastener eliminates nut and bolt failure
- Patented reinforcing edge minimizes stress breakage
- High carbon C1080 steel for superior performance on the job and specially coated for ultimate rust prevention
- Made in the USA

Item No.	Mfr. No.	Overall Length (in)
113791867	GS-1SA <sup>a</sup>	6 1/2, 9 1/2
113791866	GS-3SA <sup>b</sup>	6 1/2, 9 1/2, 12

<sup>a</sup> Includes a 2 in 1 screwdriver.

<sup>b</sup> Includes a 6 in 1 screwdriver.

**IRWIN.**

**WISE-GRIP®**

**The Original™ Curved Jaw Locking Pliers With Wire Cutter**



**Features:**

- Curved jaw with built-in wire cutter great for a variety of applications and material shapes
- Classic trigger release provides maximum locking force
- Convenient wire cutter included
- Constructed of high grade, heat-treated alloy steel for maximum toughness and durability
- Hardened teeth are designed to grip from any angle
- Hex key adjusting screw tightens to adjust pressure and draw materials together and provides a controlled release
- Backed by the IRWIN® VISE-GRIP® lifetime guarantee

Item No.	Mfr. No.	Jaw Capacity (in)	Overall Length (in)
100904530	502L3	1 7/8	10



**Curved Diagonal Cutting Pliers**



**Features:**

- CHANNELLOCK BLUE® grips for comfort
- Uses high carbon C1080 steel for superior performance on the job and specially coated for ultimate rust prevention
- High leverage
- Laser heat-treated cutting edges last longer
- Curved diagonal
- Made in the USA

Item No.	Mfr. No.	Overall Length (in)
111193258	447	7.75
111193299	449	9.54



**High Leverage Diagonal Cutting Pliers**



**Features:**

- CHANNELLOCK BLUE® grips for comfort
- Uses high carbon C1080 steel for superior performance on the job and specially coated for ultimate rust prevention
- Only CHANNELLOCK® uses a knife and anvil style cutting edge to ensure perfect mating and superior cutting edge life
- Laser heat-treated cutting edges last longer
- High leverage lap joint diagonal
- Made in the USA

Item No.	Mfr. No.	Length (in)
111193094	337	7
111004586	338	8

