

GW GEARWRENCH Combination Ratcheting Wrench



- Features:**
- Ratcheting box end needs only 5° to move vs. standard 30° for standard box end wrenches
 - Surface Drive Plus™ provides stronger grip on fasteners with up to 25% more torque

Finish: Full Polish
No. of Points: 12

Finish: Full Polish
No. of Points: 12

Inch

Item No.	Mfr. No.	Opening (in)	Overall Length (in)
102141272	9038D	1 1/4	16.764
102117738	9034	1 1/16	14.140
102102513	9032	1	13.110
102101687	9030	15/16	13.110
102101518	9028D	7/8	11.470
102100409	9026D	13/16	11.470
102101838	9022	11/16	8.870
102101839	9020	5/8	8.200
102101840	9018D	9/16	7.050
102101157	9016D	1/2	7.000
102143362	9014	7/16	6.508
102146015	9012D	3/8	6.250
102101519	9010D	5/16	5.500
102102514	9008	1/4	4.920
102142634	9036	1 1/8	15.846
102100413	9011D	11/32	5.880
102140379	9024	3/4	9.764
101486450	9040	1 7/16	19.685
101486449	9042	1 1/2	19.685
101493841	9044	1 9/16	22.638
101493061	9046D	1 5/8	22.638
101487459	9048	1 11/16	24.213
101486374	9050D	1 3/4	24.213
101487460	9052D	1 13/16	25.394
101496490	9054D	1 7/8	25.394
101493843	9056D	2	25.787
101493842	9060D	1 5/16	18.110
101497825	9062D	1 3/8	18.110

Metric

Item No.	Mfr. No.	Opening (mm)	Overall Length (in)
102102125	9134D	34	18.110
102101685	9132	32	16.760
102141153	9130D	30	15.840
102101836	9127D	27	14.140
102102126	9125D	25	13.110
102103775	9124	24	13.110
102140371	9122	22	11.470
102141154	9121	21	11.470
102140372	9120	20	11.470
102117737	9119	19	9.760
102102512	9118D	18	9.310
102102511	9117D	17	8.870
102101686	9116D	16	8.200
102141155	9115D	15	7.850
102140373	9114D	14	7.050
102101517	9113D	13	7.000
102101837	9112	12	6.750
102141270	9111	11	6.500
102103776	9110D	10	6.250
102102127	9109	9	5.880
102140374	9108D	8	5.050
102141271	9107	7	5.236
102103777	9106	6	4.920
101495013	9136	36	19.680
101493062	9141D	41	22.638
101493844	9146D	46	25.394
101485973	9150	50	25.787

GW GEARWRENCH

Combination Ratcheting Wrench Set



- Features:**
- Ratcheting box end needs as little as 5° to move vs. 30° for standard box end wrenches

Includes:

- 1/4", 5/16", 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 7/8", 15/16", 1"

Item No.	Mfr. No.	No. of Pieces
102101835	9312	13

GW GEARWRENCH

7 Piece Combination Ratcheting Wrench Set



- Features:**
- 5° ratcheting arc vs. 30° on standard combination wrenches
 - Sleek head enables access to tight spots where a ratchet will not fit

Includes:

- Set contents for 9317: 5/16", 3/8", 7/16", 1/2", 9/16", 5/8", 3/4"
- Set contents for 9417: 8 mm, 10 mm, 12 mm, 13 mm, 14 mm, 15 mm, 18 mm

Item No.	Mfr. No.	Inch/Metric
102143359	9317	Inch
102145600	9417	Metric



Ratcheting Box Wrench Set



Item No.	Mfr. No.	Inch/Metric	No. of Points	Includes
111204984	9439	Inch	12	1/4" x 5/16" 3/8" x 7/16" 1/2" x 9/16" 5/8" x 11/16" 3/4" x 7/8" Denim tool roll
105489392	9430	Metric	12	7 mm x 8 mm 9 mm x 10 mm 11 mm x 12 mm 13 mm x 14 mm 15 mm x 17 mm Denim tool roll

GW GEARWRENCH

13 Piece Inch XL Combination Ratcheting Wrench Set



- Features:**
- XL long pattern wrench for more leverage and torque
 - Ratcheting box end needs as little as 5° to move vs. 30° for standard box end wrenches
 - Surface Drive Plus™ provides stronger grip on fasteners, reduces fastener rounding and delivers up to 25% more torque

Includes:

- 1/4", 5/16", 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 7/8", 15/16", 1"

Item No.	Mfr. No.	No. of Pieces
102103761	85199	13

GW GEARWRENCH

12 Piece Metric XL Combination Ratcheting Wrench Set



- Features:**
- 5° ratcheting arc vs. 30° on standard combination wrenches
 - Up to 25% longer than standard combination ratcheting wrenches
 - Surface Drive Plus™ provides stronger grip on fasteners with up to 25% more torque

Includes:

- 8 mm, 9 mm, 10 mm, 11 mm, 12 mm, 13 mm, 14 mm, 15 mm, 16 mm, 17 mm, 18 mm, 19 mm

Item No.	Mfr. No.
102141245	85098

