

Hand, Power & Analytical Tools

STANLEY

Self-Retracting Safety Blade Utility Knife



Features:

- Durable, all metal knife body construction
- Machine screw firmly holds knife body together; screwdriver required for blade change
- Contoured handle and textured, die-cast body for slip resistance
- Interlocking nose design helps secure blade and helps prevent body separation
- Comes with hang hole for adding a wrist strap or lanyard
- Spring load blade retracts automatically when pressure on slide button is released
- Includes (1) blade
- Works with most standard utility blades

Item No.	Mfr. No.	Color
105846229	10-189P	Unpainted
106002599	10-189C	Orange

CHANNEL LOCK

Long Nose Pliers



Features:

- Crosshatch pattern on jaws grips work tightly
- With side cutter
- Only CHANNELLOCK® uses a knife and anvil style cutting edge to ensure perfect mating and superior cutting edge life
- CHANNELLOCK® uses high carbon C1080 steel for superior performance on the job and specially coated for ultimate rust prevention
- CHANNELLOCK BLUE® grips for comfort
- Made in the USA

Item No.	Mfr. No.	Jaw Length (in)	Overall Length (in)
111193086	326	2.08	6
111193292	318	2.30	8 1/2
111193083	317	2.36	8

GEARWRENCH

2 Piece Double-X™ Pliers Set



Features:

- Aligned, serrated tips for precision gripping
- Flush rivet for strength and narrow profile
- Compound joint allows access with minimal handle movement
- Jaws open greater distance than the handle for added reach in tight locations
- Dual-dipped handle for comfort and grip
- Corrosion-resistant alloy steel
- Maximum reach without exceeding center point of interference

Item No.	Mfr. No.	Plier Type
101374909	82106	45° & Straight

CRESCENT X2™ Straight Long Nose Pliers



Features:

- Long reach pliers with compound action joint for increased access in tight spaces
- Flush rivets for strength and thinner profile
- Dual material grips for added comfort
- Milled grooves in tips grip fasteners and other objects tightly

Item No.	Mfr. No.	Jaw Length (in)
110692610	PSX200C	2 3/4

OTC Heavy-Duty Snap Ring Plier Set



Features:

- Heat-treated steel "circlip" pliers for large equipment repair
- Replaceable tips and spring ratchet locking mechanism to securely hold against snap ring tension
- Internal plier's capacity 3 1/16" to 6 1/4" (78 mm to 159 mm) snap rings
- External plier's capacity 3 1/2" to 6 1/2" (89 mm to 165 mm) snap rings
- Blow-molded storage case includes extra sets of replaceable 0.12" (3 mm) dia. tips: straight, 45° and 90°

Item No.	Mfr. No.	No. of Pieces	External Ring Range (in)	Internal Ring Range (in)
110327159	4513	2	3 1/2 to 6 1/2	3 1/16 to 6 1/4

ROTOR CLIP Standard Internal Retaining Ring Pliers



Features:

- High carbon
- Heat-treated steel
- Stop and return springs
- Air-cushioned handles

Specifications

Mfr. No.	Series HO Ring Size Range	Series BHO Ring Size Range	Series VHO Ring Size Range	Series HOI Ring Size Range
RPS-100	25-31	25-31	-	62
RP-100	37-56	37-56	-	75-100
RPL-100	62-102	62-102	100-102	106-137
RP-300	106-175	106-175	106-175	143-200
RP-500	181-300	-	181-300	206-300

Item No.	Mfr. No.	Closed Width (in)	Tip Dia. (in)	Closed Length Standard Tip (in)
101464522	RPS-100	1 7/8	0.025	5 1/2
101464632	RP-100	1 7/8	0.038	5 1/2
101469291	RPL-100	1 7/8	0.047	5 1/2
101464515	RP-300	2 1/4	0.070	6 7/16
101464777	RP-500	2 1/4	0.090	9

ROTOR CLIP

Standard External Retaining Ring Pliers



Features:

- High carbon
- Heat-treated steel
- Stop and return springs
- Air-cushioned handles
- Complies with RoHS restrictions on the use of certain hazardous substances in electrical and electronic equipment

Specifications

Mfr. No.	Series SH Ring Size Range	Series BSH Ring Size Range	Series VSH Ring Size Range	Series SHI Ring Size Range	Series SHR Ring Size Range
RP-18	18-23	—	—	—	—
RP-200	25-66	25-66	—	50-78	39-47
RP-400	93-143	93-143	100-143	106-200	—
RP-600	150-350	150-175	150-350	215-325	—

Item No.	Mfr. No.	Closed Width (in)	Tip Dia. (in)	Closed Length Standard Tip (in)
101463969	RP-18	1 1/2	0.023	5 5/18
101470331	RP-200	2 1/2	0.038	5 1/2
101470931	RP-400	2 7/8	0.070	7
101471253	RP-600	4 1/4	0.115	9 1/8



Don't Forget...

Don't see a tool you need?

Visit Applied.com for a more comprehensive offering.

