

STREAMLIGHT LED Headlamp
Heroes Trust Streamlight



Features:

- Push button switch is easy to use when wearing gloves and is recessed to protect it from inadvertent activation
- Low level battery indicator visible in the face cap of each light
- Red LED flashes when battery voltage is low and batteries are near the end of their usable life
- LED is located in the reflector in between the "Low Batt" marking and functions while the light is on
- 90° tilting head features a robust ratcheting system; prevents neck fatigue
- Durable, co-molded rubber body
- IPX4 rated for water resistance; 2 meter impact resistance tested
- Adjustable elastic head strap and rubber hard hat strap
- Limited lifetime warranty
- C-ETL-US classified class I, division 2, groups A, B, C, D; class II, division 2, groups F, G; class III, T5
- Most models meet applicable European community directives

Beam Type	Bulb	Lumen Output (lm/m²)	Item No.	Mfr. No.	Battery Size	Modes
Spot	(1) LED	150	102089094	61301 ARG0 YLO	3 AAA	High, Medium or Low
Flood	(1) LED	180	113821421	61703	Rechargeable	High, Low or Strobe
	(7) LED	120	101484024	61052	3 AAA	High, Medium or Low
Spot to Flood	(4) LED	80	104272449	61050	3 AAA	High, Medium or Low
	2 LED	200	113764155	61422	3 AAA	High or Low

MOTOROLA SOLUTIONS RM Series Two-Way Radio

Authorized Business Radio Reseller

RM Series two-way radios have the business smarts to help you work better together; they combine outstanding quality with excellent affordability. With crisp, clear audio throughout the workplace and exceptional durability, RM Series radios won't quit in high noise, harsh conditions or hard use.



Features:

- **Coverage** – up to 250,000 sq ft and 20 floors
- **Battery life** – up to 15 hours per charge
- **Selectable frequencies** – VHF radios have 27 preprogrammed frequencies, MURS have five frequencies and UHF have 89 frequencies
- **Voice Annunciation** – ease of programming and channel announcement
- **Narrowband compliant** – only operates on 12.5 kHz
- **Computer programmable software** – available to easily program radios (optional accessory – programming cable required)
- Eight channel radios offer NOAA (weather)

Includes:

- Rechargeable Li-Ion battery
- Drop-in charging tray
- Charging adapter
- Swivel belt holster
- Owner's manual
- Two-year, over-the-counter exchange warranty

RM Two-Way Radios

Radio Features	RMM2050	RMU2040	RMU2080	RMU2080D	RMV2080
Frequency Band	MURS	UHF	UHF	UHF	VHF
Power/Watts	2 W	2 W	2 W	2 W	2 W
Channels (default/capable)	5	2/4	8	8	8
Interference Eliminator Codes (PL/DPL)	39/83	39/83	39/83	39/83	39/83
Pre-Programmed Frequencies	5	89	89	89	27
Cloning Capability	Y	Y	Y	Y	Y
Vox – w/ Three Sensitivity Settings	Y	Y	Y	Y	Y
Battery Life – (between charges) (hrs)	15	15	15	15	15
Channel Annunciation	Y	Y	Y	Y	Y
Scan w/ Edit List	Y	Y	Y	Y	Y
Wt. (oz)	8.6	8.6	8.6	9.0	8.9
Range – Indoors (Steel/Concrete)	220,000 sq ft	250,000 sq ft	250,000 sq ft	250,000 sq ft	220,000 sq ft
Range – Multi-Level Buildings	13 floors	20 floors	20 floors	20 floors	13 floors
Replaces RDX Model	RDM2020; RDM2080D	RDU2020	RDU2080D	RDU2080D	RDV2020; RDV2080D

Item No.	Mfr. No.	Power (W)	No. of Channels	Frequency Range
110305073	RMM2050	2	5	MURS
110305074	RMU2040	2	4	UHF
110305075	RMU2080	2	8	UHF
110305076	RMU2080D	2	8	UHF
110305077	RMV2080	2	8	VHF

All RM Series radios except RMM2050 require an FCC License.

