

# Safety Products



## GoldSpec® Safety Glasses

GoldSpec® safety glasses can be used in most general safety applications.



### Features:

- Relaxed bridge design fits most wearers
- Thin, flexible temples provide secure fit without uncomfortable pressure points
- Lens variety ensures a style for any application
- Bayonet temples with soft rubber end pieces for increased comfort
- Indoor/outdoor lens available
- CE certified

Frame Color	Lens Color	Item No.	Mfr. No.
Clear	Clear	101625767	GSZ12



## Zenon Z12 Eyewear

a clear vision of safety



### Features:

- Relaxed bridge design to fit the vast majority of users
- Thin, flexible temples provide secure fit without uncomfortable pressure points
- Lightweight, rimless design provides all day user comfort
- Lens variety assures a style for every application
- Base curve = 9.5
- Meets ANSI Z87.1+ high impact requirements

Nose Bridge: Saddle  
Frame Type: Polycarbonate

Frame Color	Lens Color	Lens Coating	Item No.	Mfr. No.
Black	Clear	Hard Coat	111659264	250-01-0000
	Gray	Hard Coat	111659263	250-01-0001
Clear	Clear	Hard Coat	111659330	250-01-0900
		Hard Coat, Anti-Fog	111659347	250-01-0920
		Uncoated	111659346	250-01-0980



## Jackson Safety\* V60 Nemesis\* RX Safety Eyewear



### Features:

- Cheater style lens with diopters for vision assistance
- Larger wraparound lens for added impact protection
- Enhanced nosepiece design for added comfort
- Neck cord included
- Meets ANSI Z87.1+ 2010 impact standard
- 99.9% UV protection

Frame Type: Nylon

Frame Color	Lens Color	Diopter Strength	Item No.	Mfr. No.
Black	Clear	+1.50	111151477	28621
		+2.00	111151476	28624
		+2.50	111151475	28627

\*Trademark of Kimberly-Clark Worldwide Inc., or its affiliates.



## Jackson Safety\* V30 Nemesis\* Safety Eyewear



### Features:

- Sporty, flexible, lightweight design
- Soft-touch temples for added comfort
- Single-lens wraparound protection
- Neck cord included (also available in reader style lenses)
- 99% UV protection
- Meets ANSI Z87.1+ 2010 standards

Nose Bridge: Enhanced w/ Integrated Ridges to Divert Sweat  
Frame Type: Nylon

Frame Color	Lens Color	Item No.	Mfr. No.
Black	Blue Mirror	111151232	14481
	Clear	111151768	25676
	Clear Anti-fog	101903032	25679
	Smoke Anti-fog	101903031	22475

\*Trademark of Kimberly-Clark Worldwide Inc., or its affiliates.



## Protégé® Safety Eyewear



### Features:

- Floating lens design offers flexibility and fit
- Ultra lightweight at 27.5 grams for all day comfort
- Secure wraparound brow expands to fit a wide range of users
- Meets ANSI Z87.1-2010 and is certified to the requirements of CSA Z94.3 standards

Frame Color	Lens Color	Lens Coating	Item No.	Mfr. No.
Metallic Black	Clear	Uvextra™ AF	111190676	S4200X
	Gray	Uvextra™ AF	111190678	S4201X



## Genesis® Safety Eyewear



### Features:

- Engineered for comfort, protection and style, Genesis® is the number one selling premium eyewear in the market, delivering an incredible range of superior product benefits
- Dual nine-base wraparound lens provides uncompromised peripheral vision and protection

- Soft flexible fingers adjust and conform to almost any nasal profile and reduce slippage
- Soft elastomer browguard diffuses and deflects impact
- Easy and economical lens replacement system
- Adjustable temple length and lens inclination
- Meets military V0 ballistic test for impact
- Meets ANSI Z87.1-2010 and is certified to the requirements of CSA Z94.3 standards
- Lifetime frame guarantee

Nose Bridge: Soft; Flexible Nose Fingers

Frame Color	Lens Color	Lens Coating	Item No.	Mfr. No.
Black	Clear	Dura-Streme™, Hard Coat, Anti-Fog	111188999	S3200D
		Ultra-dura, Hard Coat	111188997	S3200
	Espresso	Ultra-dura, Hard Coat	111189001	S3201
	Gray	Uvextreme®	111190673	S3213X

