

OIL-DRI Oil-Only Pads & Rolls



Made from highly absorbent, melt-blown polypropylene with no chemical additives. Material is naturally hydrophobic to absorb petroleum-based fluids while repelling water. Ideal for absorbing oils floating on water and perfect for any outdoor use, as product is weather-resistant.



- Features:**
- Superior fluid retention
 - Dustless
 - Hydrophobic – repels water
- Applications:**
- Motor oil
 - Benzene
 - Acrolein
 - Butyric acid
 - Isoprene

Material: Melt-Blown Polypropylene

Pad

Material Wt.	Length (in)	Width (in)	Pkg. Qty.	Item No.	Mfr. No.
Light	19	15	200	101625653	L90851*
Medium	19	15	100	101896381	L90904*
Heavy	19	15	100	101849716	L90850*

Roll

Material Wt.	Length (ft)	Width (in)	Pkg. Qty.	Item No.	Mfr. No.
Medium	150	30	1	101850750	L90781

SpillTech Oil-Only Defender™ Pads & Rolls



- Features:**
- Highly absorbent SonicBonded mat for oily spills and overspray
 - Abrasion-resistant top layer gives pads strength for everyday cleanup jobs
 - Perfect for medium-duty industrial, maintenance and general applications
 - Quickly absorbs leaks, spills and overspray to keep floors dry
 - Perforations allow you to tear pads into different sizes based on your application
 - Oil selective – repels water but absorbs oil and oil-based fluids

Color: White
Material: Polypropylene

Defender™ Pad

Material Wt.	Length (in)	Width (in)	Absorption per Pad/Roll (oz)	Pkg. Qty.	Item No.	Mfr. No.
Light	19	15	19.90	200	110867527	WPB200S*
Medium	19	15	31.62	100	110867525	WPB100M*
Heavy	19	15	37.25	100	110867524	WPB100H*

Defender™ Roll

Material Wt.	Length (ft)	Width (in)	Absorption per Pad/Roll (gal)	Pkg. Qty.	Item No.	Mfr. No.
Medium	150	15	46.10	1	113882484	WRSB150M-1
		30	46.10	2	110867555	WRB150M*
Heavy	150	15	55.20	1	113882483	WRSB150H-1
		30	55.20	2	110867567	WRSB150H*
				1	110867554	WRB150H

SpillTech Universal Defender™ Pads & Rolls



- Features:**
- Control spills and overspray to help keep floors dry and safe
 - Fast acting for quick response
 - High absorbency keeps it on the job longer
 - Ultrasonic bond points fuse layers of fibers together – mat keeps its shape even when completely saturated
 - Top layer of lint-free SpunBond fabric provides extra strength
 - “Dimples” add fast-wicking power
 - SpunBond top layer allows for better defined perforations and cleaner, easier tear-offs
 - Pads are perforated up their center at 7.5”
 - Color coding helps you visually identify the right sorbent for your needs
 - Grunge-hiding gray signifies universal sorbency for oils, coolants, solvents and water

Material: Polypropylene
Color: Gray

Defender™ Pad

Material Wt.	Length (in)	Width (in)	Absorption per Pad/Roll (oz)	Pkg. Qty.	Item No.	Mfr. No.
Single	19	15	19.90	200	110867266	GPB200S*
Medium	19	15	31.62	100	110867264	GPB100M*
Heavy	19	15	37.25	100	110867263	GPB100H*

Defender™ Roll

Material Wt.	Length (ft)	Width (in)	Absorption per Pad/Roll (gal)	Pkg. Qty.	Item No.	Mfr. No.
Medium	150	15	46.10	1	113882362	GRSB150M-1
		30	46.10	2	111323291	GRSB150M*
Heavy	150	15	55.20	1	110867287	GRB150M
		30	55.20	2	110867298	GRSB150H*
				1	113882361	GRSB150H-1
				1	110867286	GRB150H

