

**3M 3M™ Particulate Respirator 8210, N95**



- Features:**
- Helps provide worker protection against certain non-oil based particles
  - Comfortable, easy-to-use
  - Promotes greater worker acceptance, may help increase wear time
  - 3M™ proprietary filter media
  - Nose foam and adjustable noseclip help provide a secure seal and reduce eyewear fogging

- Applications:**
- Woodworking
  - Grinding
  - Sanding
  - Sweeping
  - Bagging
  - Other dusty operations

**Mask Type:** Disposable  
**Strap:** Elastic  
**Pkg. Qty.:** 20

Item No.	Mfr. No.
101879184	50-051138-46457-3

**3M 3M™ Particulate Respirator 8210V, N95**



This disposable N95 particulate respirator featuring 3M™ Cool Flow™ valve helps provide comfortable, reliable worker respiratory protection against certain non-oil based particles. Well suited for hot/dusty work settings or long periods of wear.



- Features:**
- Proprietary 3M™ Cool Flow™ valve helps keeps wearer cool
  - Cushioning nose foam
  - Adjustable noseclip helps provide a custom and secure seal
  - Advanced electrostatic media is designed for ease of breathing
  - Compatible with a variety of protective eyewear and hearing protection

**Mask Type:** Disposable  
**Strap:** Elastic  
**Pkg. Qty.:** 10

Item No.	Mfr. No.
114809792	00-051131-49711-5

**3M 3M™ Particulate Respirator 8511, N95**



- Features:**
- Helps reduce exposure to dust from sanding on particle board, drywall, nonlead paints and fiberglass insulation dust
  - M-nose clip helps provide a secure seal and helps reduce eyewear fogging
  - Includes the 3M™ Cool Flow™ exhalation valve

**Mask Type:** Disposable  
**Strap:** Elastic  
**Pkg. Qty.:** 10

Item No.	Mfr. No.
101871812	50-051138-54343-8

**WARNING**



These respirators help protect against certain airborne contaminants. Before use, the wearer must read and understand the USER Instructions provided as a part of the product packaging. A written respiratory protection program must be implemented meeting all the requirements of OSHA 1910.134 including training, fit testing and medical evaluation. In Canada, CSA standards Z94.4 requirements must be met and/or requirements of the applicable jurisdiction, as appropriate. **Misuse may result in sickness or death.** For proper use, see packaging instructions, superior, or call 3M OH&ESD Technical Service in USA at 1-800-243-4630 and in Canada at 1-800-267-4414.


**MOLDEX® N95 Particulate Respirator**



- Features:**
- Dura-Mesh® shell resists collapsing in heat and humidity
  - Molded nose bridge seals easily without a metal noseband
  - Facepiece is naturally contoured without pressure points
  - Softspun® lining for increased comfort and durability
  - Soft foam nose cushion for added comfort
  - Meets heat and flame resistance in accordance with ANSI/ISEA 110-2003 section 7.11.1
  - 100% PVC-Free®

Item No.	Mfr. No.	Size	Exhale Valve
111154733	2201N95	Small	No
111154726	2301N95	Small	Yes
111154735	2200N95	Medium/Large	No
111154708	2300N95	Medium/Large	Yes

**MOLDEX® AirWave® Disposable Respirator**



- Features:**
- Patented easy breathing, low resistance wave design
  - More air and more comfort mean more wear and compliance
  - Soft, cloth SmartStrap® allows you to adjust for a custom fit (4600 and 4800 series only)
  - Dura-Mesh® shell resists collapsing in heat and humidity
  - Meets heat and flame resistance in accordance with ANSI/ISEA 110-2003 section 7.11.1
  - 100% PVC-Free®

Size	Latex Strap		Cloth Strap	
	Item No.	Mfr. No.	Item No.	Mfr. No.
Small	111154661	4201	111154694	4601
Medium/Large	111154670	4200	111154684	4600

**Full Flange – Plus Relief from Nuisance Levels of Organic Vapors & Ozone**

Size	Cloth Strap	
	Item No.	Mfr. No.
Medium/Large	111154693	4800

**MOLDEX® 7000 Series Half Mask Respirator**



- Features:**
- Lightweight design plus extra wide sealing area provide all day comfort and increased compliance
  - Low profile, compact design fits well under welding helmets and with safety glasses
  - Mask drops down for convenient storage around the neck or locks down for custom fit
  - Maintenance made simple with very few replacement parts for cost savings
  - 100% PVC-Free®

Size	Respirator		Respirator & Organic Vapor Cartridge	
	Item No.	Mfr. No.	Item No.	Mfr. No.
Small	111154809	7001	111154843	7101
Medium	111154808	7002	111154845	7102
Large	111154807	7003	111154818	7103

