

**STANLEY** PowerLock® Tape Rule



- Features:**
- 7 ft blade standout (excludes 33-116 and 33-158)
  - Mylar® polyester film helps extend life of entire blade
  - High-impact, chrome-plated ABS case
  - Secure blade lock won't creep during measurements
  - Corrosion-resistant Tru-Zero™ end hook for accurate measurements

Item No.	Mfr. No.	Inch/Metric	Blade Length (ft)	Width (in)
106006486	33-116	Inch	16	3/4
105992157	33-158	Inch/Metric	16	3/4
105978087	33-425	Inch	25	1
106014768	33-428	Inch/Metric	26	1
105978876	33-430	Inch	30	1
105995572	33-835	Inch	35	1

Mylar® is a registered trademark of DuPont Teijin Films.



**Empire**  
True Blue® Box Level



- Features:**
- Reinforced vial locking system secures acrylic block vials and delivers long life accuracy
  - Tool-free removable, shock absorbing endcaps provide superior protection and scribing performance
  - Precision milled edges for guaranteed accuracy
  - Surface grippers prevent the level from sliding on flat or angled surfaces
  - Ergonomic grip zones enhance comfort and portability (48" + only)
  - High contrast e-BAND™ vials highlight the edge of the bubble
  - 300° viewing window maximizes range of view
  - Hang hole for ease of storage
  - Powerful rare earth magnets provide superior holding strength (magnetic models only)
  - 0.0005" accuracy in all working positions
  - Limited lifetime warranty

**Body Material:** Aircraft Aluminum  
**Vial Material:** Acrylic

Item No.	Mfr. No.	Length (in)	Height (in)	Thickness (in)
112921338	E75.24	24	2 3/4	1 1/8
112921339	E75.32	32	2 3/4	1 1/8
112921340	E75.48	48	2 3/4	1 1/8

**STANLEY** FATMAX® Tape Rules w/ BladeArmor® Coating



- Features:**
- 11 ft blade standout
  - 1 1/4" wide blade for easy readability
  - BladeArmor® coating on the first 4 1/2" maximizes durability of the blade
  - Mylar® polyester film extends life of entire blade
  - High-impact ABS case with durable rubber holds up to heavy use
  - Top-forward blade lock makes locking and unlocking easy
  - Cushion grip provides comfortable, slip-resistant hold
  - Three-rievet, corrosion-resistant Tru-Zero™ end hook for accurate measurements

Item No.	Mfr. No.	Inch/Metric	Blade Length (ft)	Blade Width (in)
105998117	33-716	Inch	16	1 1/4
106029131	33-725	Inch	25	1 1/4
106004918	33-726	Inch/Metric	26	1 1/4
105940174	33-730	Inch	30	1 1/4
106009909	33-735	Inch	35	1 1/4
105995501	33-740	Inch	40	1 1/4

Mylar® is a registered trademark of DuPont Teijin Films.



**CRESCENT**  
**Lufkin**  
Executive® Diameter Pocket Measuring Tape



- Features:**
- Designed for measuring diameters of pipe, cable, tire or any circular object
  - Polished chrome case
  - Zero falls in the same place on each side of the blade; conversion from diameter to circumference is made simply by turning the blade
  - Yellow-clad blade
  - Easy-to-read, bold graduations on yellow background
  - Spring action returns blade to case

**Blade Style:** A19

Item No.	Mfr. No.	Length (ft)	Width (in)
101878823	W606PD	6	1/4



**CRESCENT**  
**Lufkin**  
Atlas®/Nubian® Double Duty Oil Gauging Measuring Tape



- Features:**
- Recessed beneath multiple layers of nickel and chrome electroplating
  - Provides greater resistance to wear and corrosion
  - All tapes read right to left
  - Heavy-duty frame designed for years of rugged use
  - All frames include a grounding strap

**Blade Material:** Carbon Steel  
**Blade Style:** D1  
**Blade Width:** 1/2 in  
**Plumb Bob:** 590

Item No.	Mfr. No.	Blade Length (ft)
112972711	CN1290SF590N	25
112908082	CN1293SF590N	50



**Empire**  
em81 Series Heavy-Duty Magnetic I-Beam Level



- Features:**
- True Blue® vials are accurate to within 0.0005" per inch in all 10 level and plumb working positions
  - Super strong anodized aluminum I-Beam frame with milled edges for accuracy
  - Strong holding magnetic edge
  - Shock absorbing endcaps protect the frame
  - Top reading window
  - Dropped edge for added rigidity

**Color:** Black  
**Body Material:** Aluminum  
**Magnetic:** Yes

Item No.	Mfr. No.	Length (in)	Height (in)	Thickness (in)
111944586	EM81.9	9	3 7/8	3/4
111944578	EM81.10	10	3 7/8	3/4

